



TRACEABLE ACID DETERGENT FOR TANKS AND CIRCUITS

INDICATIONS

Traceable acid detergent for tanks and circuits in the Cosmetics and Pharmaceutical Industries.

INSTRUCTION FOR USE

Concentrated solution for professional use.
Used at a dilution from 3 to 7% depending on the nature of the dirt.
Rinse with process water before use.

PRECAUTIONS FOR USE

Dangerous. Follow the instructions for use (in accordance with Directive 99/45/EC and its adapted versions.

Store between +5°C and +35°C.

Made in France.

COMPOSITION

Combination of surfactants in acid environment.

PHYSICO-CHEMICAL DATA

- Clear colourless solution
- Density at +20°C: approx. 1,40
- pH of pure product at +20°C: between 0 and 1
- pH at dilution of 1%: 1,5

PACKAGING

25 kg can: 2304.547

2304GB-2013.04.A